


# Type T Glassfibre Insulated Flat Pair thermocouple cable / wire (IEC)



**General Description** Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.

**Cable Length** 10m, 25m, 50m, 100m

**Cable Type** Flat pair cable

**Core / Strands** 1/0.315mm

**Conductor Cross Section 1/0.315** 0.078  
(mm<sup>2</sup>)

**Outer Colour** Brown & White

**+ Colour** Brown

**- Colour** White

**Drain Wire** No



<b>Insulation Material</b>	Glassfibre insulated
<b>Loop Resistance 1/0.315 (Ohms per combined metre)</b>	6.5
<b>Max. Temperature</b>	+350°C (short periods up to 400°C)
<b>Min. Temperature</b>	-60°C
<b>+ Conductor</b>	Copper
<b>- Conductor</b>	Constantan
<b>Screen</b>	No
<b>Standards Met</b>	Colour code (cores & jacket) to IEC-584-3
<b>Thermocouple Type</b>	T
<b>Tolerance</b>	Class 2