


General Purpose Pt100 Silicone Rubber Lead - Type RTD / PRT



General Description	Suitable for general purpose industrial & commercial use
Sensor Type	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B, 4 wire
Probe Diameter	6.0mm
Probe Length	Various
Sheath Material	316 stainless steel sheath.
Cable Length	2m
Cable Type	flexible silicone rubber insulated
Core / Strands	7/0.2mm
Cable Termination	Bare Tails
Termination Type	4-wire tails allows connection to any PT100 instrument 2, 3 or 4 wire
Max. Temperature	+200°C

Min. Temperature -50°C

Accuracy Class B

Number of Wires 4

