



# LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

## **PFA Cable Tidy IEC Exposed Junction Thermocouple with Fitted Mini Plug - Type K - PFA Twin Twisted - 2M Length**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Cable Tidy Thermocouple with Fitted Miniature IEC Plug, PFA Twin Twisted or Flat Pair.

A complete precision fine wire, high sensitivity exposed junction thermocouple, with a fitted miniature connector.

### **Need Your Temperature Sensor calibrated?**

Traceable to ISO17025 (UKAS) calibration standards, Labfacility offer a choice of a 3 or 5 point traceable calibration using our in-house calibration facility, you can select any temperature points between -10°C & +200°C.

**Please be aware that if you add a calibration option to your order you will be contacted regarding delivery information**

### **Specifications**

## **Specifications**

<b>Product Code</b>	XE-7028-001
<b>General Description</b>	A complete, precision fine wire, high sensitivity thermocouple with a fitted miniature connector and cable tidy.
<b>Sensor Type</b>	Exposed Junction
<b>Thermocouple Type</b>	K IEC
<b>Cable Length</b>	2M
<b>Cable Type</b>	PFA Twin Twisted Insulated Wire
<b>Termination Type</b>	Miniature flat pin plug, colour coded in accordance IEC 584
<b>Max. Temperature</b>	Rated 220°C continuous
<b>Tolerance</b>	Class 1
<b>Standards Met</b>	IEC 584
<b>Connector Type</b>	Plug
<b>Connector Size</b>	Miniature