

Therma Hygrometer and Thermometer



[Click here to view product](#)

Product Code	XE-3985-001
General Description	The 6500 therma-hygrometer incorporates a clear custom LCD with °C, %rh, max/min, hold and dew point indication. An auto power-off facility turns the instrument off after 10 minutes? non-use.
Accuracy	Temperature: ± 1 °C over the range 5 to 45 °C otherwise ± 1.7 °C Humidity: $\pm 3\%$ (20 to 80 %rh)
Resolution	Temperature: 0.1°C/°F Humidity: 0.1%rh
Dimensions	25 x 56 x 128mm
Max. Temperature	70°C

Min. Temperature	-20°C
Weight	160 grams
Power Supply	3 x 1.5-volt AAA. Battery life: 10000 hours
Sensor Type	temperature: silicone bandgap ? humidity: capacitance polymer