


## PFA insulated Twin Twisted IEC Exposed Junction Thermocouple with Miniature Plug - Types K,J,T



[Click here to view product](#)

|                            |   |
|----------------------------|---|
| <b>Product Code</b>        | XE-3530   |
| <b>General Description</b> | Fast response, welded exposed junction                      |
| <b>Sensor Type</b>         | Exposed Junction  |
| <b>Thermocouple Type</b>   | K, J & T  |
| <b>Cable Length</b>        | 1, 2, 5 & 10m   |
| <b>Cable Type</b>          | Teflon® PFA insulated twin-twisted lead                     |
| <b>Core / Strands</b>      | 1/0.2mm, 1/0.315mm, 7/0.2mm, 1/0.5mm                        |
| <b>Termination Type</b>    | Miniature flat pin plug, colour coded in accordance IEC 584 |
| <b>Max. Temperature</b>    | +250°C  |
| <b>Min. Temperature</b>    | -75°C   |

|                       |           |
|-----------------------|-----------|
| <b>Tolerance</b>      | Class 1   |
| <b>Standards Met</b>  | IEC-584-3 |
| <b>Connector Type</b> | Plug      |
| <b>Connector Size</b> | Miniature |