

GM816 Hot Wire Anemometer Wind Meter Anemometer / Digital Anemometer



[Click here to view product](#)

| | |
|---------------------------------|--|
| Product Code | XE-4003-001 |
| Model | GM816 Hot Wire Anemometer Wind Meter Anemometer / Digital Anemometer |
| Accuracy | +/- 5% |
| Air Temp: Accuracy | +/- 2°C, +/- 3.6F |
| Air Temp: Range | -10~45°C, 14~113°F |
| Air Temp: Resolution | Resolution 0.2°C, 0.36°F |
| Air Velocity: Range | 0.3 - 30m/s, 0 - 90km/h, 0 - 5860ft/min, 0 - 65mph, 0 - 55Knots |
| Air Velocity: Resolution | 0.1m/s, 0.3km/h, 19ft/min, 0.2mph, 0.2Knots |
| Air Velocity: Threshold | 0.1m/s, 0.3km/h, 39ft/min, 0.2mph, 0.1Knots |
| Battery | 1 x 3V CR2032 battery (Not Included) |

| | |
|------------------------------|--|
| Colour | Yellow / Black |
| Current Consumption | 3mA Approx |
| Dimensions | 10.5 x 4.5 x 2 cm / (4.13 x 1.77 x 0.79) |
| Operating Humidity | less than or equal to 90%RH |
| Operating Temperature | -10~45°C (14~113°F) |
| Weight | 105g / 3.7oz |
| Storage Temperature | -40~60°C, -40~140°F |
| Thermometer | NTC Thermometer |