

GM816 Hot Wire Anemometer Wind Meter Anemometer / Digital Anemometer



Model	GM816 Hot Wire Anemometer Wind Meter Anemometer / Digital Anemometer
Accuracy	+/- 5%
Air Temp: Accuracy	+/- 2°C, +/- 3.6F
Air Temp: Range	-10~45°C, 14~113°F
Air Temp: Resolution	Resolution 0.2°C, 0.36°F
Air Velocity: Range	0.3 - 30m/s, 0 - 90km/h, 0 - 5860ft/min, 0 - 65mph, 0 - 55Knots
Air Velocity: Resolution	0.1m/s, 0.3km/h, 19ft/min, 0.2mph, 0.2Knots
Air Velocity: Threshold	0.1m/s, 0.3km/h, 39ft/min, 0.2mph, 0.1Knots
Battery	1 x 3V CR2032 battery (Not Included)
Colour	Yellow / Black
Current Consumption	3mA Approx



Dimensions 10.5 x 4.5 x 2 cm / (4.13 x 1.77 x 0.79)

Operating Humidity less than or equal to 90%RH

Operating Temperature -10~45°C (14~113°F)

Weight 105g / 3.7oz

Storage Temperature -40~60°C, -40~140°F

Thermometer NTC Thermometer

