



## IEC Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Type K with Standard Plug Termination - 6.0mm Washer Hole Size



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Specifications****Specifications**

<b>Product Code</b>	XE-5633-001
<b>General Description</b>	Thermocouple housed in a washer eyelet
<b>Thermocouple Type</b>	K
<b>Thermocouple Junction</b>	Grounded tip for quick response
<b>Cable Length</b>	2m
<b>Cable Type</b>	Glassfibre insulated, stainless steel overbraided
<b>Core / Strands</b>	7/0.2mm
<b>Termination Type</b>	Standard Plug
<b>Max. Temperature</b>	+350°C
<b>Standards Met</b>	IEC
<b>Washer</b>	3.5mm, 4.0mm, 5.0mm, 6.0mm, 8.0mm & 10.0mm clearance hole available
<b>Series</b>	Washer Thermocouple