


0.75mm Diameter Plain pot seal with 1 Metre of PFA insulated lead, 7/0.2mm flat pair with IEC tails ? Insulated or Grounded



[Click here to view product](#)

Product Code	XE-0182
General Description	Plain pot seal (200°C) with 1 Metre of PFA insulated lead, 7/0.2mm flat pair with tails.
Sensor Type	Mineral Insulated
Thermocouple Type	K
Element/hot junction	Single element, junction insulated or grounded from sheath
Probe Diameter	0.75mm
Probe Length	50, 100, 150, 250mm
Sheath Material	K - Stainless steel 316
Pot Type	Plain (+200°C)
Cable Length	1M

Cable Type	PFA Teflon® insulated flat pair cable and tails (colour coded to IEC 584)(Max Temp 250°C)
Core / Strands	7/0.2mm
Termination Type	Bare Tails
Max. Temperature	+750°C
Min. Temperature	-100°C
Tolerance	Class 1
Standards Met	In accordance with IEC 584