




# Digital Household Thermometer Hygrometer with rear magnet



[Click here to view product](#)

|                            |   |
|----------------------------|---|
| <b>Product Code</b>        | XE-4352-001   |
| <b>Model</b>               | LDTH-8  |
| <b>General Description</b> | Digital Household Thermometer Hygrometer with rear magnet |
| <b>Type</b>                | Timer-Thermometer 2 in 1                                  |
| <b>Accuracy</b>            | +/- 3%  |
| <b>Readings</b>            | Timer range: 99 Min 59 Sec                                |
| <b>Resolution</b>          | 0.1°C(0.2°F)  |
| <b>High Alarm Level</b>    | High temperature alarm function                           |
| <b>Battery</b>             | CR2430  |
| <b>Cable Length</b>        | Wire: 120cm length  |



|                              |  |
|------------------------------|--|
| <b>Length</b>                | 10m  |
| <b>Colour</b>                | White  |
| <b>Dimensions</b>            | 118mm x 60mm x 7.5mm                                   |
| <b>Functions</b>             | °C/°F  |
| <b>Function #1</b>           | Continuous: 33°F- 140°F                                |
| <b>Display Type</b>          | LCD  |
| <b>Operating Humidity</b>    | 25%-98% RH   |
| <b>Temperature Range</b>     | -50-70°C (-58-158°F)                                   |
| <b>Probe Material</b>        | 304 stainless steel                                    |
| <b>Weight</b>                | 86g  |
| <b>Sensor Type</b>           | Sensirion SHT30  |
| <b>Standards Met</b>         | CE, FCC, ROHS  |
| <b>Construction</b>          | Eco-friendly ABS plastic + Stainless steel front shell |
| <b>Display</b>               | FSLCD  |
| <b>Important Information</b> | Support stand or magnetic mounting options             |