

ANSI Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Terminating in Standard Plug - 3.5mm Washer Hole Size



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.



Specifications

Specifications

XE-0928-001
Thermocouple housed in a washer eyelet
K
Grounded tip for quick response
2m
Glassfibre insulated,stainless steel overbraided
7/0.2mm
Standard plug termination with cable clamps
+350°C
ANSI
3.5mm clearance hole
Washer Thermocouple