

ANSI Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid Terminating in Bare tails - 3.5mm Washer Hole Size



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.



Specifications

Specifications

| XE-0934-001 |
|--|
| Thermocouple housed in a washer eyelet |
| K |
| Grounded tip for quick response |
| 2m |
| Glassfibre insulated,stainless steel overbraided |
| 7/0.2mm |
| Bare Tails |
| +350°C |
| ANSI |
| 3.5mm clearance hole |
| Washer Thermocouple |
| |