



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Washer Thermocouple, Glassfibre insulated Cable with Stainless Steel Over-Braid - Type K JIS with Standard Plug Termination and 8.0mm Washer Hole Size



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Specifications**Specifications**

Product Code	XE-0977-001
General Description	Thermocouple housed in a washer eyelet
Thermocouple Type	K JIS
Thermocouple Junction	Grounded tip for quick response
Cable Length	2m
Cable Type	Glassfibre insulated, stainless steel overbraided
Core / Strands	7/02.mm
Termination Type	Standard plug termination with cable clamps
Max. Temperature	+350°C
Standards Met	JIS (Japanese Industrial Standards)
Washer	8.0mm clearance hole