

Hermetically Sealed Wire RTD Sensor

Hermetically Sealed Tip



**2.6mm
Nominal Wire Diameter**

[Click here to view product](#)

Product Code	XE-6380
General Description	An IP67 wire RTD sensor that is hermetically sealed for use in corrosive or wet environments
Sensor Type	Hermetically sealed Pt100 class A 4 wire resistance thermometer
Cable Length	1, 2 & 5m
Cable Type	4 wire flexible 7/0.2mm stranded conductors (24AWG) with 75mm tails
Core / Strands	7/0.2mm (24AWG)
Termination Type	75mm Bare Tails
Max. Temperature	+260°C
Min. Temperature	-30°C

Tolerance	Class A
Standards Met	IP67
Important Information	Pressure tested at 40 PSI as standard