

## Thermocouple Connector Aluminium Panel with Type T ANSI Standard Sockets - 12 Way



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

### **Pre-assembled Standard Thermocouple Connector Panels**

A pre-assembled standard horizontal panel assembly designed for use with thermocouples or leads with standard plugs. Robust and perfect for mounting in control rooms, test stands, laboratory applications, control rooms, and more. They support calibration codes including K, J, T with quick wire sockets and can accommodate 1-24 way circuits, with a maximum temperature range up to +120°C.

Supplied pre-fitted with

#### Standard Fascia Sockets

12 way circuit

Type T ANSI calibration

Maximum temperature 120°C

### **Typical Applications**

OEMs

Instrumentation panel builders

Control rooms

Test Rigs and Skids

### **Specifications**

|                            |                                                                                          |
|----------------------------|------------------------------------------------------------------------------------------|
| <b>Product Code</b>        | XE-7525-001                                                                              |
| <b>General Description</b> | Accepts standard round pin plug connector. Nylon clip for quick, simple fixing to panel. |
| <b>Thermocouple Type</b>   | T ANSI                                                                                   |
| <b>Number of Ways</b>      | 12 Way                                                                                   |
| <b>Connector Size</b>      | Standard                                                                                 |
| <b>Connector Type</b>      | Fascia Mounting Socket                                                                   |
| <b>Colour</b>              | Blue                                                                                     |
| <b>Dimensions</b>          | H66mm x W259mm                                                                           |

|                   |                        |
|-------------------|------------------------|
| Max. Temperature  | 120°C                  |
| +Positive Contact | Copper                 |
| -Negative Contact | Copper Nickel          |
| Standards Met     | BS EN 50212:1997. RoHS |