

ANSI High Temperature Glassfibre Twin Twisted Exposed Welded Tip Thermocouple Type K with Miniature Plug Termination - 10M Length



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Need Your Temperature Sensor calibrated?

Traceable to ISO17025 (UKAS) calibration standards, Labfacility offer a choice of a 3 or 5 point traceable calibration using our in-house calibration facility.

Please be aware that if you add a calibration option to your order you will be contacted regarding delivery information.

Specifications**Specifications**

Product Code	XE-5645-001
General Description	Fast response, welded exposed junction. Good temperature resistance (not suitable in fluids)
Sensor Type	Exposed Junction
Thermocouple Type	K
Cable Length	10M
Cable Type	high temperature glassfibre insulated twisted cable
Core / Strands	1/0.711mm conductors (21awg)
Cable Termination	Miniature Plug
Max. Temperature	700°C
Min. Temperature	0°C
Tolerance	Tolerance to ANSI MC96.1 Class 2
Standards Met	Colour code to ANSI MC96.1
Connector Type	Plug
Connector Size	Miniature



Colour	Yellow
Series	Exposed Junctions